

系列名 Series Name

EPS-CEM

电机简称 Motor Simplified Name

CEM-30



单编码器 Single Encoder

型号 Actuator Full Name	货品编码 Product Code	抱闸/非抱闸 With Brake/Without Brake
EPS-CEM-30-C-B	1104010000121100	B (with brake)
EPS-CEM-30-R-B	1104010000221100	B (with brake)

产品参数 Product Parameters

产品名称 Item Name	CEM-30	
减速机类型 Reducer type	-	智能减速机 Smart joint reducer
额定电压 Nominal Voltage	V	24
额定电流 Rated Current	A	2.5
最高瞬时电流 Highest instantaneous current	A	5(≤10s)
额定功耗 Rated Power	W	60
通讯方式 Communication Mode	-	CAN
额定扭矩 Nominal Torque	N.m	30
最高瞬时扭矩 Max Instaneous Torque	N.m	50(≤10s)
额定输出转速 Rated output speed	RPM	15
最高峰值转速 Maximum peak speed	RPM	20
最高重复定位精度 Repeat Positioning Accuracy	-	0.01
外形尺寸 Dimensions	mm	D76*90
电机重量 Motor weight	g	730

尺寸安装图 Installation Drawing

