


X4-10-L Interface Description




X4-10-L Packaging Information



List:

- A. Power Supply + CAN BUS Communication Cable *2
- B. 120R plug-in resistor *1
- C. UL2547 4C 28AWG Shielded Cable (Black/Yellow/White/Red)50cm *2
- D. CAN BUS Communication Module *1
- E. RJ45 Adapter Plate V2.0 *1 (For Ethercat version)


X4-10-L Accessories Marking Instructions




Power Supply + CAN BUS Communication Cable

① XT30(2+2)-F Connector


② White Line	CAN_L Network Signal Terminal 26AWG 20cm
③ Yellow Line	CAN_H Network Signal Terminal 26AWG 20cm
④ Red Line	VCC Positive Power Supply 18AWG 20cm
⑤ Black Line	GND Negative Power Supply 18AWG 20cm



120R plug-in resistor




UL2547 4C 28AWG Shielded Cable



CAN BUS Communication Module

① CAN-L	CAN_L Network Information Terminal
② CAN-H	CAN_H Network Information Terminal
③ CAN-G	GND Ground
④ OFF	120Ω Terminal Resistance
⑤ ON	120Ω Terminal Resistance



RJ45 Adapter Plate V2.0

① RJ45 Connector	Wired Network Interface
② PE	Motor Housing Ground / Shield Ground
③ R-	The module reflects the control commands of the master station
④ R+	The master station feedbacks the module status data
⑤ T-	The module sends status feedback to the master station
⑥ T+	The master station sends control commands to the module

Notes: Each order includes one USB-CAN adapter. For additional adapters, please contact our sales team to place an order.

Notes: Ethercat version - Each order includes one RJ45 adapter. For additional adapters, please contact our sales team to place an order.