

Series Name

EPS-RH

Motor Simplified Name

RH-17



Dual encoder

Actuator Full Name	Communication	With Brake/Without Brake	Gear ratio
EPS-RH-17-100-E-N-D	EtherCAT & CAN BUS	N (without brake)	100
EPS-RH-17-100-E-B-D	EtherCAT & CAN BUS	B (with brake)	100

* 1. The standard model supports brake or without brake.


* 2. The standard model supports both CAN BUS & EtherCAT.

* 3. The standard model does not have waterproof function. For IP54, please contact sales before ordering.


* 4. 50:1 gear ratio is available, please contact sales to confirm the lead time before ordering.

Installation Drawing

EPS-RH-17-100-E-N-D



EPS-RH-17-100-E-B-D



Product Parameters


Parameters	Unit	RH-17
Gear ratio	—	50 100
Input Voltage	V	48
No Load Speed	RPM	60 30
No Load Current	A	0.6 0.6
Rated Speed	RPM	50 25
Rated Torque	N.m	17.5 35
Rated Power	W	91
Rated Current	A(rms)	4.7
Peak Torque	N.m	27 54
Peak Current	A(rms)	7.4
Motor Back-EMF Constant	Vdc/Krpm	19.2
Module Torque Constant	N.m/A	3.7 7.4
Motor Phase Resistance	Ω	0.7
Motor Phase Inductance	mH	0.47
Pole Pair	—	10
3 Phase Connection	—	Y
Backlash	Arcsec	< 40
Radial Load	Static Load	KN
	Dynamic Load	KN
Axial Load	Static Load	KN
	Dynamic Load	KN
Inertia	N	kg.m ²
	B	kg.m ²
Encoder Type	—	Dual Encoder ABS-17BIT (Input) ABS-17BIT (Output)
Repeat Position Accuracy	Degree	< 0.01
Communication	—	EtherCAT & CAN BUS
Weight	N	Kg
	B	Kg
Insulation Grade	—	F

*** Rated torque test method:** When the ambient temperature is 24 degrees Celsius (no other heat dissipation methods), the test is performed at the rated speed. The motor torque reaches temperature balance under the condition of a temperature rise of 60 degrees Celsius, and the long-term working point is the rated torque value of the motor.

Stall Torque Data

	Torque (N.m)	Temperature Rise (°C)	Stall Time (s)	Phase Current (Arms)
RH-17	52.5	15	15	6.9
	70	7	10	9.8
	87.5	35	8	11.9

RH-17 Interface Description



RH-17 Packaging Information



List:

- A. Power Supply Cable *2
- B. CAN BUS Communication Cable *2 / Bleeder Resistor Cable *1 / Multi-turn battery Cable *1
- C. 120Ω Terminal Resistance *1
- D. EtherCAT Communication Cable *2
- E. CAN BUS Communication Module *1
- F. RJ45 Adapter Plate V1.0 *1 (For Ethercat version)

RH-17 Accessories Marking Instructions

