


X10-200 Interface Description



X10-200 Packaging Information




List:

- A. Power Supply Cable *2
- B. 120R plug-in resistor *1
- C. EtherCAT Communication Cable *2
- D. CAN BUS Communication Module *1
- E. RJ45 Adapter Plate V2.0 *1 (For Ethercat version)

X10-200 Accessories Marking Instructions


A



B




C



D



E



Power Supply Cable		
① XT60H-F Connector		
② Red Line	VCC Positive Power Supply	12AWG 20cm
③ Black Line	GND Negative Power Supply	12AWG 20cm

120R plug-in resistor		

EtherCAT Communication Cable		
① SH 1.0 5pin		
② Red Line	EtherCAT Communication Signal Transmission Line	28AWG 500mm
③ White Line	EtherCAT Communication Signal Transmission Line	28AWG 500mm
④ Yellow Line	EtherCAT Communication Signal Transmission Line	28AWG 500mm
⑤ Black Line (thin)	EtherCAT Communication Signal Transmission Line	28AWG 500mm
⑥ Black Line (thick)	Motor Housing Ground / Shield Ground	28AWG 500mm

CAN BUS Communication Module		
① CAN-L	CAN_L Network Information Terminal	
② CAN-H	CAN_H Network Information Terminal	
③ CAN-G	GND Ground	
④ OFF	120Ω Terminal Resistance	
⑤ ON	120Ω Terminal Resistance	

RJ45 Adapter Plate V2.0		
① RJ45 Connector	Wired Network Interface	
② PE	Motor Housing Ground / Shield Ground	
③ R-	The module reflects the control commands of the master station	
④ R+	The master station feedbacks the module status data	
⑤ T-	The module sends status feedback to the master station	
⑥ T+	The master station sends control commands to the module	

Notes: Each order includes one USB-CAN adapter. For additional adapters, please contact our sales team to place an order.

Notes: Ethercat version - Each order includes one RJ45 adapter. For additional adapters, please contact our sales team to place an order.